



## MT-6 tunnel egg washer

## Description

**Capacity:** 19 200 eggs/hour

**Replaces:** 50 people

**Power supply:** 40-50 kW 400 V 3/N/PE 50/60 Hz

**Dimensions:** 4507x2000x1765 mm

**Minimal workspace:** 3000x6000 mm

**Compressed air:** n/a

**Weight:** 1000 kg



**Water:** water from client's installation

**Operated by:** 4 persons

**Drain:** required

**Compatibility:** VEL-30, UVC-6, RZ-6, UDTJ-150/500




The MT-6 washes the eggs in a 3D fashion thanks to the use of specially designed rotating brushes which clean all of the eggs' surfaces. This allows for an exceptional level of cleanliness. First, the eggs are fed into the machine with the use of an integrated belt feeder. There, thanks to the use of specially profiled rollers, the eggs are rotated along their axis, while specially designed brushes wash the eggs at every angle, which results in a 3D washing effect. After washing, the eggs are transported into a drying section, where they are dried by a stream of warm air. The machine is made out of stainless steel EN 1.4301 (AISI 304).



DATE  
20.01.2021  
PROJECT  
DOK-LAY-EN12.1

AUTHOR  
ML

4507



**MT-6 tunnel egg washer**

**Typical workplaces:** egg breaking facilities, bakeries, confectioneries, pasta making, companies

**Capacity:** 15200 eggs/hour

**Power supply:** 40-50 kW 400 V 3~/N/PE 50/60 Hz

**Water connection:** water from client's installation

**Compressed air connection:** N/A

**Minimal workspace:** 3000 x 6000 mm

**Dimensions:** 4507 x 2000 x 1765 mm

**Operated by:** 4 persons

**Minimal wall clearance:** the rear side - 600 mm

**Additional information:** Drainage access required

<b>A</b>	control panel
<b>B1/B2/B3</b>	connection: electrical/water/air
<b>C</b>	eggs input
<b>D</b>	eggs outlet
<b>E</b>	egg yolks outlet
<b>F</b>	egg white outlet
<b>G</b>	egg white outlet

**OVO TECH**

EGG PROCESSING MACHINES

All rights reserved  
The design and technical specifications  
is the sole property of OVO-TECH.  
Any use of this product, including  
reproduction, is strictly prohibited  
without O's written permission & strictly  
prohibited.